



PlugTail® Tamper-Resistant Spec Grade Receptacles, 20A, 125V PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

## Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

Smooth wall plate.

No exposed terminals create a finger safe application before, during, and after installation.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Crimped and welded contacts.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Pre-wired with one welded pre-stripped wire lead to facilitate switched receptacle circuit applications.

Auto-ground clip assures positive ground.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Brown
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Commercial, Indoor, Tamper-Resistant	Application Sector	Commercial

---

Standard	UL 498	Warranty Type	1-Year Limited Warranty
----------	--------	---------------	-------------------------

---

Type	Outlet
------	--------

---

### Dimensions

---

Product Width US	1.5 in	Product Depth US	0.625 in
------------------	--------	------------------	----------

---

Product Height US	2.75 in
-------------------	---------

---

### Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

### Technical Information

---

Is Tamper-Resistant	Yes	Phase	3
---------------------	-----	-------	---

---

Number of Wires	3	Amperage	20 A
-----------------	---	----------	------

---

Number of Poles	Double Pole	Wire Size	14 - 10 AWG
-----------------	-------------	-----------	-------------

---

Indoor/Outdoor	Indoor	Voltage	125.0 V
----------------	--------	---------	---------

---