



Pass and Seymour

PlugTail® 20A 125V Extra Heavy Duty Hospital-Grade Tamper-Resistant Duplex Receptacle, White

Part No. PTTR63HW



PlugTail® Extra Heavy-Duty Hospital Grade Tamper-Resistant Receptacles, 20A, 125V PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

No exposed terminals create a finger safe application before, during, and after installation.

Crimped and welded contacts.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

For covering patents, see www.legrand.us/patents.

PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only

Available in 'SP' series in Standard, Junior-Jumbo, and Jumbo sizes.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Auto-ground clip assures positive ground.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007860603
Country Of Origin	Mexico	Number of Receptacles	2

Outlet Type	Tamper-Resistant	Application Sector	Commercial, Hospital Grade
-------------	------------------	--------------------	----------------------------

Standard	cULus UL498, FEDSPEC	Type	Outlet
----------	----------------------	------	--------

Dimensions

Product Width US	1.625 in	Product Depth US	0.9 in
------------------	----------	------------------	--------

Product Height US	3.281 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Is Tamper-Resistant	Yes
---------------------	--------------------------	---------------------	-----

Temperature Rating	-40° - 60° C	Amperage	20 A
--------------------	--------------	----------	------

Number of Poles	Double Pole	Wire Size	12 AWG
-----------------	-------------	-----------	--------

Indoor/Outdoor	Indoor
----------------	--------
