



PlugTail information, visit our PlugTail Headquarters.



## Features & Benefits

|   |  |
|---|--|
| .036 inch thick, brass, triple-wipe power contacts for lasting retention.                     | Plated steel wrap strap design for maximum durability and corrosion resistance.  |
| No exposed terminals create a finger safe application before, during, and after installation. | Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.                 |
| Crimped and welded contacts.  | Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing. |
| Large brass contacts snugly terminate on device blade terminals.                              | Pre-stripped connector leads fasten to conductors, easier than standard pigtails.  |
| Auto-ground clip assures positive ground.   | For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> .                                 |

## Specifications

### General Info

|                    |                        |                   |  |
|--------------------|------------------------|-------------------|--|
| Product Line       | Pass & Seymour         | Country Of Origin | China                                  |
| Application Sector | Residential/Commercial | Standard          | CSA Listed, cUL, UL Listed, RoHS, FSUL |

### Dimensions

|                   |         |                  |        |
|-------------------|---------|------------------|--------|
| Product Width US  | 1.7 in  | Product Depth US | 1.2 in |
| Product Height US | 2.75 in |                  |        |

Listing Agencies / 3rd Party Agencies

cULus Listed                      Yes

Technical Information

|            |                    |                          |                    |
|------------|--------------------|--------------------------|--------------------|
| Phase      | Single             | Frequency Rating         | 60 Hz              |
| Connection | Built-In Connector | Class                    | IG                 |
| Amperage   | 20 A               | Type of Indicators       | LED, Audible Alarm |
| Voltage    | 125 V              | Environmental Conditions | UL94 V2            |