



Wattstopper
PIR Dimmable Wall Switch Sensor, Universal, 120V, White, USA
Part No. PW-101D-W-U



The PW-100D and PW-101D passive infrared (PIR) dimmable wall switch sensors can turn light OFF and ON based on occupancy. It is characterized by high sensitivity to small and large movements, appealing aesthetics, and a variety of features.

Features & Benefits

Collection consolidated to white option

High sensitivity and dense coverage for exceptional performance

Defaults to Manual-ON operation for maximum energy savings

Color-matched lens and low profile for appealing design

Pushbutton dimming control and optional locked preset level for many lighting types

Selectable operation, walk-through, test and presentation modes for increased energy savings and convenience

Part of a comprehensive line of PIR, Ultrasonic and Dual Technology wall switch sensors

Specifications

General Info

Product Line	Wattstopper	Replaced by Part Number	PW-101D-W
Color	White	Finish	Glossy
UPC Number	754182938506	Country Of Origin	United States
Product Series	PW-100	Features	Adjustable Time Delay, Air Gap Switch, Dimming, Indicator Lights, Light Level Sensor, Sensitivity Adjustment, Vandal Resistant Lens
Switch Type	Motion Sensor, Push	Installation Location	Wall
Included	Sensor Mask	Application Sector	Commercial

Standard	UL, cUL, BAA, TAA	Warranty Type	5-Year
Type	Sensor, Switch		
Dimensions			
Product Width US	1.8 in	Product Weight US	0.3 lb
Product Volume US	35.1 cu in	Product Depth US	1.9 in
Product Height US	4.1 in		
Additional Information			
Product Environmental Profile	Yes		
Technical Information			
Operating Temperature Min	32 °F	Timer Type	DIP Switch
Load Rating	700 W @ 120 VAC	Has Battery	No
Sensor Coverage Pattern	180 deg	Sensor Type	Occupancy
Operating Temperature Max	131 °F	Sensor Mounting Height	4 ft
Number of Buttons	1	Number of Rockers	0
Sensor Technology	Passive Infrared (PIR)	Timer Duration	5-30 Minutes
Indicator	PIR Detection LED	Input Voltage	120 V
Requires Neutral Wire	Yes	Line Frequency	50 Hz, 60 Hz
Indoor/Outdoor	Indoor	Mounting Type	In-Wall
On Function	Selectable Auto/Manual	Operating Temperature	0°-55°C, 32°-131°F
Operating Humidity	5-95% RH (Non-Condensing)	Sensing Range	Major motion 35 x 30 ft, Minor motion 20 x 15 ft
Wire Connection Type	Flying Leads	Engraving Type	Blank
Storage Temperature	23° - 176° F, -5° - 80° C		