



PlugTail® Split Circuit Spec Grade Duplex Receptacle 20 A 125 V, Light Almond  
 For detailed PlugTail® information, visit our PlugTail® Headquarters.

## Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

Plated steel wrap strap design for maximum durability and corrosion resistance.

No exposed terminals create a finger safe application before, during, and after installation.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Large brass contacts snugly terminate on device blade terminals.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Pre-wired with one welded pre-stripped wire lead to facilitate switched receptacle circuit applications.

Auto-ground clip assures positive ground.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

Color	Ivory	UPC Number	785007000177
Country Of Origin	Mexico	Product Line	Pass & Seymour
Application Sector	Commercial	Standard	cULus UL498

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

---

## Technical Information

---

Number of Poles	Double Pole	Voltage	125 V
Dielectric Strength	Withstands 2000V minimum	Temperature Rating	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact
Wire Size	PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only	Number of Wires	3
Environmental Conditions	Flammability: UL94 V2		

---