



Wattstopper  
Discontinued - PIR Wall Switch Occupancy Sensor, 2 Relays, 120/277V, Ivory  
Part No. PW-200-I



The PW-200 passive infrared (PIR) wall switch sensor turns lights ON and OFF based on occupancy. It contains two relays for controlling two independent lighting loads or circuits, and a variety of features.

## Features & Benefits

High sensitivity and dense coverage for exceptional performance

Color-matched lens and low profile for appealing design

Defaults to Auto-ON to 50% operation for maximum energy savings

Sensor coverage tested to NEMA Guide Publication WD 7-2000

Vandal resistant lens combines precise coverage with durability

Choice of Manual-ON or Auto-ON operation, selectable for each relay

Service mode allows sensor to operate as a service switch in the unlikely event of a failure

Two relays for control of two separate lighting loads or circuits

Selectable operation, walk-through, test and presentation modes for increased energy savings and convenience

Defaults to Auto-ON to 50% operation for maximum energy savings

Detection Signature Processing eliminates false triggers and provides immunity to RFI and EMI

Selectable walk-through mode turns lights off three minutes after the room is initially occupied if no motion is detected after the first 30 seconds

In automatic mode, sensor returns automatically to Auto-ON after lights are turned off manually; ideal for presentations

## Specifications

### General Info

Product Line	Wattstopper	Replaced by Part Number	PW-302-I
Color	Ivory	UPC Number	754182919338
Country Of Origin	China	Features	IR (Infrared), Motion Sensor

Switch Type	Motion Sensor	Application Sector	Commercial
Warranty Type	5-Year		
<b>Dimensions</b>			
Product Width US	4.0 in	Product Weight US	0.35 lb
Product Volume US	63.0 cu in	Product Depth US	5.0 in
Product Height US	3.15 in		
<b>Additional Information</b>			
RoHS Conformant	Yes	DesignLights Consortium Qualified System	Yes
Security	Yes	Product Environmental Profile	Yes
<b>Technical Information</b>			
Response Frequency	50/60 Hz	Sensor Type	Occupancy
Number of Buttons	2	Amperage	4.3 A
Indicator	LED Light	Wattage	1200 W
Sensing Range	Major motion 35 x 30 ft, Minor motion 20 x 15 ft	Voltage	120/277 V
Connection Type	Wired		