



Pass and Seymour PlugTail® Split Circuit Spec Grade Receptacles, 20A, 125V, Light Almond Part No. PT5362SCLA



PlugTail® Split Circuit Spec Grade Duplex Receptacle 20 A 125 V, Light Almond For detailed PlugTail® information, visit our PlugTail® Headquarters.

Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.	Plated steel wrap strap design for maximum durability and corrosion resistance.
No exposed terminals create a finger safe application before, during, and after installation.	Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.	Crimped and welded contacts.
Large brass contacts snugly terminate on device blade terminals.	Pre-stripped connector leads fasten to conductors, easier than standard pigtails.
Pre-wired with one welded pre-stripped wire lead to facilitate switched receptacle circuit applications.	Auto-ground clip assures positive ground.
For covering patents, see www.legrand.us/patents .	For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here .

Specifications

General Info

UPC Number	785007000160	Country Of Origin	Mexico
Product Line	Pass & Seymour	Application Sector	Commercial
Standard	cULus UL498		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Number of Poles	Double Pole	Voltage	125 V
Dielectric Strength	Withstands 2000V minimum	Temperature Rating	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact
Wire Size	PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only	Number of Wires	3

Environmental
Conditions

Flammability: UL94 V2
