



Wiremold  
RC7AM2TC Assembled Furniture Feed Poke-Thru Device  
Part No. RC7AM2TCGY



2" trade size conduit stem, complete with one 3/4" trade size conduit and two 1/2" trade size adapters and closure plugs. Finish flange/cover assembly available in painted gray (GY), black (BK), brushed plated brass (BS), and brushed aluminum (AL). NOTE: Assembled with scrub water gasket. For use on tile or carpet floors. RC9AM2TC Series Poke-Thru Devices require a 3" (76mm) diameter hole. Not designed to work with bare concrete or terrazzo. Floor covering thickness 1/8" minimum.

## Features & Benefits

- 2" trade size conduit stem, complete with one 3/4" trade size conduit and two 1/2" trade size adapters and closure plugs
- Finish flange/cover assembly available in painted gray (GY), black (BK), brushed plated brass (BS), and brushed aluminum (AL)
- NOTE: Assembled with scrub water gasket
- For use on tile or carpet floors
- RC9AM2TC Series Poke-Thru Devices require a 3" (76mm) diameter hole
- Floor covering thickness 1/8" minimum
- Floor covering thickness 1/8" minimum

## Specifications

### General Info

Product Line	Wiremold	Color	Gray
UPC Number	786564008712	Country Of Origin	Mexico
Construction	Assembled	Cover Style	Furniture Feed
Number of Knockouts	1	Application Sector	Commercial, Education, Healthcare, Hospitality
Standard	UL Fire Classified, cULus, NEC	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Poke-Thru		

## Dimensions

---

Product Weight US	4.0 lb	Core Hole Size	3 in
-------------------	--------	----------------	------

---

Knockout Size	2 in
---------------	------

---

### Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	E2961	cULus Listed	Yes
---------------------	-------	--------------	-----

---

### Additional Information

---

RoHS Compliant	Yes
----------------	-----

---

### Technical Information

---

Floor Type	Carpet, Tile	Service Capacity	Dual
------------	--------------	------------------	------

---

Fire Rating	2 hr	Cable Entry	CONDUIT
-------------	------	-------------	---------

---