



Wattstopper
Resi Multi-Way Convertible Occupancy Sensor White
Part No. RH-250-W



The RH-250 Passive Infrared (PIR) Multi-way Occupancy Sensor provides automatic lighting shutoff for a variety of applications including those with multiple switch locations. It offers optional automatic lighting activation.

Features & Benefits

Collection consolidated to white option

Adjustable time delay

Ideal for hallways, stairwells and large rooms with multiple entrances

Automatic-off control with multi-way capability

Lighted pushbutton for visibility in darkened rooms

Choice of manual-on or automatic-on operation

Specifications

General Info

Product Line	Wattstopper	Replaced by Part Number	PW-301-W
Color	White	Finish	Glossy
UPC Number	754182921492	Country Of Origin	China
Product Series	RH-250	Features	Adjustable Time Delay, Indicator Lights, Light Level Sensor, Locator Light
Switch Type	Motion Sensor	Installation Location	Wall
Included	Mounting Screws	Application Sector	Commercial, Residential
Standard	UL, cUL, Compliant with Nonresidential CA Title 24 requirements, Complies with 2011 NEC requirements	Warranty Type	5-Year

Type	Sensor, Switch
------	----------------

Dimensions

Product Width US	1.69 in	Product Weight US	0.3 lb
------------------	---------	-------------------	--------

Product Volume US	27.8 cu in	Product Depth US	1.8 in
-------------------	------------	------------------	--------

Product Height US	4.2 in
-------------------	--------

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Operating Temperature Min	32 °F	Timer Type	Trimpot
---------------------------	-------	------------	---------

Load Rating	600 W @ 120 VAC	Has Battery	No
-------------	-----------------	-------------	----

Sensor Coverage Pattern	180 deg	Sensor Type	Daylight, Occupancy
-------------------------	---------	-------------	---------------------

Operating Temperature Max	131 °F	Sensor Mounting Height	4 ft
---------------------------	--------	------------------------	------

Number of Buttons	1	Number of Rockers	0
-------------------	---	-------------------	---

Sensor Technology	Passive Infrared (PIR), Photosensor	Timer Duration	15 Seconds, 5 Minutes, 15 Minutes, 30 Minutes
-------------------	-------------------------------------	----------------	-----------------------------------------------

Number of Poles	Multi-Location, Single Pole	Indicator	PIR Detection LED
-----------------	-----------------------------	-----------	-------------------

Input Voltage	120 V	Line Frequency	60 Hz
---------------	-------	----------------	-------

Indoor/Outdoor	Indoor	Sensor Coverage	600 sq ft
----------------	--------	-----------------	-----------

Mounting Type	In-Wall	On Function	Selectable Auto/Manual
---------------	---------	-------------	------------------------

Operating Temperature	0°-55°C, 32°-131°F	Operating Humidity	5-95% RH (Non-Condensing)
-----------------------	--------------------	--------------------	---------------------------

Sensing Range

24 x 25 ft

Wire Connection Type

Flying Leads

Engraving Type

Blank

Storage Temperature

23° - 176° F, -
5° - 80° C
