



radiant Collection
RADIANT LED DIMMER 250W SP/3W W
Part No. RHL373PW



Upgrade your space with precise dimming control and exceptional style. This dimmer from the radiant® Collection is optimized for use with LED 2-wire bulbs and fixtures compliant with the SSL 7A standard for energy efficiency. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Designed to save energy, this dimmer is for use with LED bulbs and fixtures also designed to the SSL 7A standard for efficiency. For use in both single-pole and 3-way applications.

Low-profile paddle switch offers smoother On/Off control, while a separate, ergonomic slider allows you to adjust light levels with precision.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

Constant memory features returns lights to their previous level after a power failure or outage.

No derating* required for 2-gang applications. *Reducing the maximum wattage a dimmer can handle. This is sometimes required for multi-gang applications.

Features durable, high-impact resistant thermoplastic construction.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	Country Of Origin	China
Features	Locator Light	Switch Type	Paddle, Slider
Number of Switches	1	Application Sector	Residential
Warranty Type	Limited Lifetime Warranty	Type	Dimmer

Dimensions

Product Width US	1.29 in	Product Depth US	1.0 in
Product Height US	3.18 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Number of Gangs	1	Amperage	2.1 A
Bulb Compatibility	CFL, Halogen, Incandescent, LED	Number of Poles	3-Way, Single Pole
Wattage	300 W	Mounting Type	Box
Voltage	120 V		