




radiant Collection
radiant® Single-Pole/3-Way Occupancy Sensor
Part No. RRW600UTC



Simplify control while saving energy, with the radiant® Occupancy Sensor. Automatically turning the light on when someone enters a room, and shutting it off when the room is empty, this sensor includes an adjustable timed delay for shut off, as well as additional settings for more flexible control. Part of the radiant® Collection, it features clean lines and smooth paddle action for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Works with various lights/bulbs, including: Incandescent, LED, fluorescent, compact fluorescent (CFL), magnetic low-voltage (MLV) and electronic low-voltage (ELV), 1/6 hp.

Customize how you want the light to turn on with three control settings.

Features an adjustable time delay, letting you set the automatic shut-off after a specified window of time. Delay settings range from 30 seconds to 30 minutes after the room is vacated.

Installs easily in place of a standard light or fan (single-pole) switch. No neutral wire required.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

The secret for always turning the lights off? A device that does it for you automatically. Perfect for bathrooms, hallways, closets, and garages.

Specifications

General Info

Color	White	UPC Number	785007496598
Country Of Origin	China	Product Line	Pass & Seymour
Application Sector	Residential	Standard	cULus

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Number of Poles	Single Pole, 3-Way	Voltage	120 V
Sensitivity	60Hz	Mounting Type	Box
Target Size	180°	Sensing Range	600 sq ft
Load	120VAC	Response Frequency	60 Hz
Environmental Conditions	Indoor Use Only		
