




Pass and Seymour
Combination Openings, 1 Toggle Switch and 1 Blank, Two Gang, 302/304 Stainless Steel
Part No. SS113



Combination Wall Plate, 1 Toggle Switch and 1 Blank, 2-Gang, 302/304 Stainless Steel

Features & Benefits

Type 302/304 Stainless Steel, non-magnetic: .032" nominal thickness. Brushed finish.

This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion. Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.

Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide. Packaged in protective film, with finish-matching screws.

Variety of special plated finishes. Paintable to match plastic plates.

Can be silk-screened or engraved, and custom punched with over 300 opening styles.

Specifications

General Info

| | | | |
|-------------------|-----------------------------------|--------------------|-------------------------|
| Product Line | Pass & Seymour | Color | Stainless Steel |
| Finish | Metallic | UPC Number | 785007129410 |
| Country Of Origin | United States | Features | Combination |
| Wall Plate Type | Blank, Combination, Toggle Switch | Application Sector | Commercial, Residential |
| Standard | CSA | Type | Wall Plate |

Dimensions

| | | | |
|-------------------|---------|------------------|--------|
| Product Width US | 4.56 in | Product Depth US | 0.2 in |
| Product Height US | 4.5 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|------------|-----|--------------|-----|
| CSA Listed | Yes | cULus Listed | Yes |
|------------|-----|--------------|-----|

Additional Information

Product Environmental Profile Yes

Technical Information

| | | | |
|-----------------|------------------|-------------|---------------|
| Cutout | Toggle and Blank | Thickness | 0.032 in |
| Number of Gangs | 2 | Wire Size | #14 - #10 AWG |
| Indoor/Outdoor | Indoor | Orientation | Horizontal |
