




## Pass and Seymour

Combination Openings, 1 Blank & 1 Single Receptacle, Two Gang, 302/304 Stainless Steel  
Part No. SS147

Combination Wall Plate, 1 Blank & 1 Single Receptacle, Two Gang, 302/304 Stainless Steel



### Features & Benefits

|   |  |
|---|--|
| Type 302/304 Stainless Steel, non-magnetic: .032" nominal thickness.  | Brushed finish.  |
| This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion.                                | Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist. |
| Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide. | Packaged in protective film, with finish-matching screws.  |
| Variety of special plated finishes.   | Paintable to match plastic plates.   |
| Can be silk-screened or engraved, and custom punched with over 300 opening styles.                                  |  |

### Specifications

#### General Info

|            |              |                   |               |
|------------|--------------|-------------------|---------------|
| UPC Number | 785007129496 | Country Of Origin | United States |
|------------|--------------|-------------------|---------------|

|              |                |                    |                        |
|--------------|----------------|--------------------|------------------------|
| Product Line | Pass & Seymour | Application Sector | Residential/Commercial |
|--------------|----------------|--------------------|------------------------|

|          |        |
|----------|--------|
| Standard | UL 514 |
|----------|--------|

#### Listing Agencies / 3rd Party Agencies

|            |     |
|------------|-----|
| CSA Listed | Yes |
|------------|-----|

#### Technical Information

|        |                             |           |          |
|--------|-----------------------------|-----------|----------|
| Cutout | Blank and Single Receptacle | Thickness | 0.032 in |
|--------|-----------------------------|-----------|----------|