



Pass and Seymour

PlugTail® Industrial Extra Heavy Duty Spec Grade Tamper-Resistant Receptacles, 15A, 125V, White

Part No. PTTR62W



PlugTail® Industrial Extra Heavy-Duty Spec Grade Tamper-Resistant Receptacles, 15A, 125A

Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

No exposed terminals create a finger safe application before, during, and after installation.

Crimped and welded contacts.

Large brass contacts snugly terminate on device blade terminals.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Extra heavy-duty 0.050" thick brass mounting strap for superior performance and durability.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

| | | | |
|--------------------|----------------|-------------------|-----------------|
| Product Line | Pass & Seymour | Color | White |
| UPC Number | 785007860276 | Country Of Origin | Mexico |
| Application Sector | Commercial | Standard | UL 498, FEDSPEC |

Dimensions

| | | | |
|------------------|----------|------------------|----------|
| Product Width US | 1.625 in | Product Depth US | 0.866 in |
|------------------|----------|------------------|----------|

| | |
|-------------------|---------|
| Product Height US | 2.75 in |
|-------------------|---------|

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|---------------------|-------------|-----------|-------------|
| Is Tamper-Resistant | Yes | Phase | Three |
| Number of Wires | 3 | Amperage | 15 A |
| Number of Poles | Double Pole | Wire Size | 14 - 10 AWG |