



Pass and Seymour
PlugTail® Extra Heavy Duty Hospital Grade Tamper-Resistant Receptacles, 20A, 125V, Ivory
Part No. PTTR63HI



PlugTail® Extra Heavy-Duty Hospital Grade Tamper-Resistant Receptacles, 20A, 125A

Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

No exposed terminals create a finger safe application before, during, and after installation.

Crimped and welded contacts.

Large brass contacts snugly terminate on device blade terminals.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Extra heavy-duty 0.050" thick brass mounting strap for superior performance and durability.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
UPC Number	785007860573	Country Of Origin	Mexico
Application Sector	Commercial	Standard	cULus UL498

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Number of Wires	3
---------------------	--------------------------	-----------------	---

Temperature Rating	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact	Number of Poles	Double Pole
--------------------	---	-----------------	-------------

Wire Size	PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only	Voltage	125 V
-----------	---	---------	-------

Environmental Conditions	Flammability: UL94 V2		
--------------------------	-----------------------	--	--
