


Double gang wallplate for Key Locking Series lock switch.
Smooth 302/304 Stainless steel.



Features & Benefits

Type 302/304 Stainless Steel, non-magnetic: .032"
nominal thickness. Brushed finish.

This alloy contains 18% chromium and 8% nickel
for superior resistance to corrosion. Recommended for use in food processing plants, dairies, chemical plants,
and other industrial, institutional, and commercial applications where
corrosive atmospheres exist.

Standard, Jumbo, and Tandem plates available, as
well as special Panel plates up to 5-gangs high and
10-gangs wide. Packaged in protective film, with finish-matching screws.

Variety of special plated finishes. Paintable to match plastic plates.

Can be silk-screened or engraved, and custom
punched with over 300 opening styles.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	United States
Application Sector	Residential/Commercial	Standard	CSA

Dimensions

Product Width US	4.56 in	Product Depth US	0.2 in
Product Height US	4.5 in		

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Cutout For KL Series Locking Switch ONLY Thickness 0.032 in

Number of Gangs 2
