



Pass and Seymour
Strain Relief Liquid-Tight Grips
Part No. STBN100SF

Straight male, liquid tight grips for non metallic type a flexible conduit. 1" npt, 12" mesh length.



Features & Benefits

Liquid-Tight grips are woven of stainless steel mesh with zinc plated steel or malleable iron bodies and nuts for corrosion resistance.

They are used to connect liquid-tight flexible conduit to electrical enclosures to prevent conduit pullout.

Each fitting is supplied with an insulated throat to provide conductor insulation and protect against damage by flexing, heat expansion and contraction.

Liquid-Tight grips are recommended in the wiring of motors and any electrical enclosure where liquid-tight conduit is subject to motion or strain.

Specifications

General Info

UPC Number	785007185102	Country Of Origin	Mexico
Product Line	Pass & Seymour	Application Sector	Industrial
Construction	Various Types of Pulling, Support and Strain Relief Grips	Standard	UL/CSA Approval (consult factory)

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	CSA Listed	Yes
--------------	-----	------------	-----

Technical Information

Mounting	Consult the Factory for Mounting Recommendations	Cable Size	NPT Size: 1; Mesh Length: 12
Capacity	Various Cable Diameter Ranges	Load	Strain Relief Grips are designed to prevent tension from being transferred to junctions and terminals on electrical cord, cable and conduit, therefore providing a more secure electrical structure.