



Pass and Seymour  
Discontinued - PlugTail® Commercial Passive Infrared (PIR) Wall Switch Sensor, White  
Part No. PTWSP250W



## Features & Benefits

Detection Signature Analysis provides high immunity to RFI and EMI.

Integrated light level sensor works from 10 to 150 footcandles.

Compatible with all electronic and magnetic ballasts, PL lamp ballasts, compact fluorescent.

Adjustable time delay of 30 seconds to 30 minutes.

Dual 120/277VAC operation, Adjustable sensitivity from 20% to 100%, 180 degree coverage of up to 900 sq. ft.

Patented voltage drop protection and zero crossing circuitry.

No exposed terminals create a fingersafe application before, during, and after installation.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

|                    |                       |                         |                              |
|--------------------|-----------------------|-------------------------|------------------------------|
| Product Line       | Pass & Seymour        | Replaced by Part Number | WS-301-W, WS250W             |
| Color              | White                 | Country Of Origin       | Mexico                       |
| Application Sector | Commercial/Industrial | Standard                | CSA Listed, cULus, UL Listed |

### Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

### Technical Information

|             |         |                    |       |
|-------------|---------|--------------------|-------|
| Target Size | 180 deg | Response Frequency | 60 Hz |
|-------------|---------|--------------------|-------|

|                          |                 |               |            |
|--------------------------|-----------------|---------------|------------|
| Sensor Type              | Occupancy       | Sensing Range | 900 sq ft  |
| Sensitivity              | 60Hz            | Load          | 120/277VAC |
| Environmental Conditions | Indoor Use Only |               |            |