



Wattstopper
PIR 0-10V Dimming Wall Switch Occupancy Sensor, 120/277V, Grey
Part No. PW-311-G



The PW-311 passive infrared (PIR) dimming wall switch sensor can turn lights OFF and ON based on occupancy and allow the user to increase or decrease the lighting level. It works with 0-10 VDC dimming drivers and ballasts to control lighting loads including LEDs.

Features & Benefits

Vandal resistant lens combines precise coverage with durability

Optional Smart Light Level adapts ambient light hold off threshold to meet user needs

Test mode allows quick and easy verification of coverage

LED indicates occupancy detection

Presentation mode may be deactivated to allow Auto-ON operation after 15 second time delay

Selectable walk-through mode turns lights off three minutes after the room is initially occupied if no motion is detected after the first 30 seconds

Selectable audible and/or visual alerts for impending shutoff

Specifications

General Info

Product Line	Wattstopper	Color	Gray
Finish	Glossy	UPC Number	754182939039
Country Of Origin	China	Product Series	PW-310
Features	Adjustable Time Delay, Dimming, Indicator Lights, Light Level Sensor, Sensitivity Adjustment, Vandal Resistant Lens	Switch Type	Motion Sensor
Installation Location	Wall	Included	Sensor Mask

Application Sector	Commercial	Standard	UL, cUL, E101196, UL 924, Complies with 2017 NEC requirements, RoHS
Warranty Type	5-Year	Type	Sensor, Switch
Dimensions			
Product Width US	1.8 in	Product Weight US	0.3304 lb
Product Volume US	13.3 cu in	Product Depth US	1.8 in
Product Height US	4.1 in		
Additional Information			
RoHS Compliant	Yes		
Technical Information			
Operating Temperature Min	32 °F	Timer Type	DIP Switch
Load Rating	1000 W @ 120 VAC, 1200 W @ 240/277 VAC	Has Battery	No
Sensor Coverage Pattern	180 deg	Sensor Type	Occupancy
Operating Temperature Max	131 °F	Sensor Mounting Height	4 ft
Number of Buttons	2	Number of Rockers	0
Sensor Technology	Passive Infrared (PIR)	Timer Duration	5-30 Minutes
Number of Poles	Multi-Location, Single Pole	Indicator	PIR Detection LED
Input Voltage	120/230/240/277 VAC	Requires Neutral Wire	No
Line Frequency	50 Hz, 60 Hz	Indoor/Outdoor	Indoor
Mounting Type	In-Wall	On Function	Selectable Auto/Manual

Operating Temperature	0°-55°C, 32°-131°F	Operating Humidity	5-95% RH (Non-Condensing)
Sensing Range	Major motion 35 x 30 ft, Minor motion 20 x 15 ft	Wire Connection Type	Flying Leads
Engraving Type	Icon	Storage Temperature	23° - 176° F, -5° - 80° C
