



Pass and Seymour
Rotary R Series Dimmer, White
Part No. R600WV



RFI Rotary Dimmer 600W

Features & Benefits

Slimmer design -- the trimmest rotary dimmers, 1/4 in. less depth than the leading competitor's models. Easy-to-grip knob with soft, contemporary curves goes with any d: cor. Interchangeable with older-style knobs.

Excellent RFI/EMI filtering performance -- won't impact sensitive electronic devices. Pre-stripped leads speed termination.

No de-rating of 600 watt models in multi-gang applications. Leaves more room in the box for faster, easier installation.

Makes small adjustments in lighting levels easier. Illuminated models are easy to find in the dark.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Gloss	UPC Number	785007045888
Country Of Origin	China	Features	Color Change Kit
Switch Type	Push, Rotary, Single Pole	Number of Switches	1
Application Sector	Residential	Standard	UL Listed
Warranty Type	Limited Lifetime Warranty	Type	Dimmer

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	95219	cULus Listed	Yes
---------------------	-------	--------------	-----

Technical Information

Load Rating	120V 600W (Halogen), 120V 600W (Incandescent)	Operating Cycles	100000
Dimming Compatibility	Forward Phase	Frequency Rating	60 Hz
Number of Gangs	1	Bulb Compatibility	Halogen, Incandescent
Number of Poles	Single Pole	Wire Size	#14 - #10 AWG
Requires Neutral Wire	No	Indoor/Outdoor	Indoor
Mounting Type	Wall Box	Wire Connection Type	Flying Leads
Voltage	120 VAC		