



Pass and Seymour  
Tamper-Resistant Commercial Grade Receptacles, Brown, TR20  
Part No. TR20



Tamper-Resistant Commercial Grade Receptacle, 20A, 125V, Brown  
For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

## Features & Benefits

Dual mechanical shutter system to help prevent insertions of foreign objects.

Auto-ground clip assures positive ground.

Backed-out tri-drive steel terminal screws. Side wire only.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

High Impact resistant nylon face.

Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Brown
UPC Number	785007241631	Country Of Origin	Mexico
Application Sector	Commercial	Standard	cULus UL498, CSA C22.2 No. 42

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

### Technical Information

Dielectric Strength	Withstands 1500V minimum	Connection	Side wire
Number of Wires	3	Temperature Rating	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +50°C, minimum -40°C without impact
Number of Poles	Double Pole	Wire Size	#14 - #10
Voltage	125 V	Environmental Conditions	Flammability: UL94 V2