



Ortronics
28awg Reduced diameter C6A/10G channel cord Red 20FT
Part No. RDC61020-02

RDC610 Modular Patch Cord, red, 20', reduced diameter, 28 AWG, cat6a channel four-pair UTP stranded PVC/CM.



Features & Benefits

- Each cord is 100% factory tested: Ensures every cord shipped support Category 6a channel specifications.
- Reduced cable diameter: Tighter bend radiuses & occupy less cable management space supporting more airflow
- Premium plug designed for reduced OD 28AWG patch cable: Protects performance through the plug termination
- Snagless plug design: Protects plugs when routing through cable managers or pathways.
- Premium 28AWG conductor cordage: Reliable performance and durable cord life.
- Backwards compatible to Category 6, and 5e: Supports lower category installations and components.
- Improved cable flexibility: Supports simple routing and cable management

Specifications

General Info

| | | | |
|--------------|-------------------|--------------------|------------------------|
| Product Line | Ortronics | Color | Red |
| UPC Number | 662875853473 | Country Of Origin | Mexico |
| Features | Reduced Diameter | Application Sector | Commercial, Industrial |
| Standard | FCC | Warranty Type | 5-Year |
| Type | Copper Patch Cord | | |

Dimensions

| | | | |
|-------------------|---------|--------------|-------|
| Product Length US | 20.0 FT | Cable Length | 20 ft |
|-------------------|---------|--------------|-------|

Additional Information

| | | | |
|----------------|-----|-------------------------------|-----|
| RoHS Compliant | Yes | Product Environmental Profile | Yes |
|----------------|-----|-------------------------------|-----|

Technical Information

| | | | |
|-----------------|-----|---------------------------|--------|
| Jacket Material | PVC | Operating Temperature Min | -10 °C |
|-----------------|-----|---------------------------|--------|

| | | | |
|-----------------------------|-------|------------|--------|
| Category Performance Rating | Cat6a | Wire Gauge | 28 AWG |
|-----------------------------|-------|------------|--------|

| | | | |
|------------------|---------------------------|-----------------------|--------------|
| Storage Humidity | 0-90% RH (Non-Condensing) | Plating Specification | 50 µ in Gold |
|------------------|---------------------------|-----------------------|--------------|

| | | | |
|--------------------|-------------|-------------|----------|
| Jacket Application | Riser Rated | Bend Radius | 0.794 in |
|--------------------|-------------|-------------|----------|

| | | | |
|---------------------|------------|-------------------|----------------|
| Shielded/Unshielded | Unshielded | Termination Style | Pre-Terminated |
|---------------------|------------|-------------------|----------------|

| | | | |
|---------------------|----------|---------------------------|-------|
| Conductor Stranding | Stranded | Operating Temperature Max | 60 °C |
|---------------------|----------|---------------------------|-------|

| | | | |
|---------------|-----------|----------------|----------|
| Jacket Rating | CMR Rated | Cable Diameter | 0.191 in |
|---------------|-----------|----------------|----------|

| | | | |
|-------|--------------------|-----------------------|-----------|
| Braid | Non-braided Wiring | Operating Temperature | -10°-60°C |
|-------|--------------------|-----------------------|-----------|

| | | | |
|--------------------|---------------------------|--------------------|--------|
| Operating Humidity | 0-90% RH (Non-Condensing) | Conductor Material | Copper |
|--------------------|---------------------------|--------------------|--------|

| | | | |
|---------|---------|---------------------|--------------|
| Voltage | 300.0 V | Storage Temperature | -40° - 60° C |
|---------|---------|---------------------|--------------|
