



Energy savings and code compliance can be easily achieved through automatic plug load control via wireless RF communication between the Plug Load RF Signal Pack (RFP) and the Plug Load RF Receptacle.

Features & Benefits

Wireless control of plug load via RF communication and integral relay.

Product meets requirements of UL498B: Receptacles with integral switching means.

Simple, three-step binding process for wireless communication with RF Single Pack

Feed-thru capability allows for downstream control of multiple receptacles.

LED Indicator Light on the receptacle guides binding process and indicated power to the receptacle.

Auto-ground eliminates the necessity to terminate grounding conductor in device.

Receptacle compliant with 2014 NEC, CA Title 24, and ASHRAE 90.1

Binding button on face also serves as a manual override.

Corrosion-resistant plated steel strap locked into face and back body to resist pulling away from face/body assembly.

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Permanently molded face offers clear identification of controlled receptacle for end users.

Specifications

General Info

Product Line	Pass & Seymour	Color	Light Almond
--------------	----------------	-------	--------------

Country Of Origin	China
-------------------	-------

Dimensions

Product Width US	1.73 in	Product Depth US	1.25 in
------------------	---------	------------------	---------

Product Height US	2.68 in
-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Amperage	15 A
----------	------
