



Tamper-Resistant Heavy-Duty Decorator Spec Grade Single Receptacle, Back and Side Wire, 20A, 125V

Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects.	Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.	Backed-out tri-drive brass terminal screws for faster installation.
Internal screw-pressure-plate back and side wire capability.	Two back wire holes for additional wiring flexibility.
.032 inch thick brass triple-wipe power contacts.	Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.
For covering patents, see www.legrand.us/patents .	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007004991	Country Of Origin	Mexico
Number of Receptacles	1	Features	Decorator Style, Heavy Duty Steel Mounting Strap
Outlet Type	Tamper-Resistant	Application Sector	Commercial
Wall Plate Included	No	Standard	UL498, CSA C22.2 No. 42
Warranty Type	1-Year Limited Warranty	Type	Outlet

Dimensions

Product Width US	1.322 in	Product Depth US	1.188 in
------------------	----------	------------------	----------

Product Height US	2.635 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Operating Temperature Min	-40 °C	Dielectric Strength	Withstands 2000V minimum
---------------------------	--------	---------------------	--------------------------

Is Tamper-Resistant	Yes	Connection Location	Back and Side
---------------------	-----	---------------------	---------------

Connection	Back and side wire	Number of Wires	3
------------	--------------------	-----------------	---

Operating Temperature Max	60 °C	Temperature Rating	-40° - 60° C
---------------------------	-------	--------------------	--------------

Amperage	20 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
-----------	-------------	----------------	--------

NEMA Configuration Code	5-20R	Operating Temperature	-40°-60°C
-------------------------	-------	-----------------------	-----------

Wire Connection Type	Internal Pressure Plates	Voltage	125.0 V
----------------------	--------------------------	---------	---------

Environmental Conditions	Flammability: UL94 V2
--------------------------	-----------------------
