



For right angle turns on same surface. Cover stop permits neat butting of 2000C Cover. Two couplings included.

## Features & Benefits

For right angle turns on same surface. Cover stop permits neat butting of 2000C Cover. Two couplings included.

## Specifications

### General Info

|                   |               |                    |              |
|-------------------|---------------|--------------------|--------------|
| Product Line      | Wiremold      | UPC Number         | 786776084740 |
| Country Of Origin | United States | Application Sector | Commercial   |

|          |  |      |          |
|----------|--|------|----------|
| Standard | cULus Listed Base & Blank Cover: File E4376<br>Guide RJBT. Multioutlet Assemblies: File<br>E15191 Guide PVGT. Fittings: File E41751<br>Guide RJPR. Base & Blank Cover & Plugmold<br>Series w/Snapcoil Harness: Meets Article 386<br>of NEC. Meets Section 12-3032 of CEC.<br>Plugmold Wired Sections: Meets Article 380<br>of NEC. Meets Section 12-3032 of CEC. | Type | Plugmold |
|----------|--|------|----------|

### Dimensions

|                   |         |
|-------------------|---------|
| Product Weight US | 0.18 lb |
|-------------------|---------|

### Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | E41751 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

### Trade Programs

|       |     |
|-------|-----|
| USMCA | Yes |
|-------|-----|

Additional Information

|                |     |                               |     |
|----------------|-----|-------------------------------|-----|
| RoHS Compliant | Yes | Product Environmental Profile | Yes |
|----------------|-----|-------------------------------|-----|

Technical Information

|          |         |                          |                        |
|----------|---------|--------------------------|------------------------|
| Amperage | 15 A    | Enclosure Type           | Stainless Steel        |
| Voltage  | 125.0 V | Environmental Conditions | Dry interior locations |