



Pass and Seymour

Tamper-Resistant Construction Spec Grade Single Receptacles, Back & Side Wire, 20A, 125V, Ivory

Part No. TR5351I



Tamper-Resistant Construction Spec Grade Single Receptacle Back & Side Wire 20amp 125volt BrownFor detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Dual mechanical shutter system to help prevent insertions of foreign objects.

.032 inch thick brass triple-wipe power contacts for lasting retention.

Auto-ground clip assures positive ground.

Backed-out tri-drive steel terminal screws. Side wire capability.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.

Corrosion-resistant plated steel strap is locked in to the face and back body to resist pulling away from the face/body assembly.

Easily accessed break-off line-contact connecting tab for fast and easy split-circuitwiring.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Color	Ivory	UPC Number	785007241976
Country Of Origin	Mexico	Product Line	Pass & Seymour
Application Sector	Commercial	Standard	UL498, CSA C22.2 No. 42

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	140596
--------------	-----	---------------------	--------

Technical Information

Number of Poles	Double Pole	Voltage	125 V
Connection	Back and side wire	Dielectric Strength	Withstands 2000V minimum
Temperature Rating	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact	Wire Size	#14 - #10
Number of Wires	3	Environmental Conditions	Flammability: UL94 V2
