



Designed for commercial markets with strength and durability in mind, this combination USB charger receptacle features 2.1A overall USB charging capability and is compatible with USB 2.0 & 3.0 devices.

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles page](#).

Features & Benefits

2.1 A USB type A receptacle charges faster than other USB receptacles eliminates the need for bulky AC adapters.

Compact Design Tamper-Resistant receptacle and two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices.

Back and side wire terminals accommodates #14 AWG - #10 AWG stranded and solid wire.

Tamper-Resistant, patented shutter system prevents improper insertion of foreign objects. Meets 2011 National Electrical Code: Tamper-Resistant requirements.

Stainless steel auto-ground clip assures positive ground.

Zink-plated ground terminal screw

For covering patents, see www.legrand.us/patents. Wire Size: #14 - #10 AWG Copper Conductor Only

Specifications

General Info

| | | | |
|--------------------|----------------|-------------------------|----------------------------------------------|
| Product Line | Pass & Seymour | Replaced by Part Number | TR5362USBI |
| Color | Ivory | Country Of Origin | China |
| Application Sector | Commercial | Standard | CSA Listed, ETL Lsted, FSUL, UL Listed, RoHS |

Additional Information

Product Environmental Profile Yes

Technical Information

| | | | |
|--------------------------|--------------------------|---------------------|-------------------|
| Dielectric Strength | Withstands 2000V minimum | Is Tamper-Resistant | Yes |
| Phase | Single | Connection | Side & Back Wired |
| Number of Wires | 3 | Temperature Rating | -40° - 60° C |
| Amperage | 20 A | Number of Poles | Double Pole |
| Wire Size | 14 - 10 AWG | Voltage | 125.0 V |
| Environmental Conditions | UL94 V2 | | |
