



5' Plugmold Multioutlet System with 5 single outlets, GB

Features & Benefits

Steel Raceway. Provides superior strength for any dry location installation.

Available in Ivory ScuffCoat or gray baked enamel finish. The durable ScuffCoat provides a durable, scratch-resistant finish while the gray baked enamel compliments the décor or can be painted.

Single-and-dual-gang boxes. Wire devices into the raceway system or protect a Plugmold® strip with a surge or GFCI device.

Single, alternating circuit, and isolated ground receptacles. Meets virtually any job requirement.

Snapicoil harnesses of prewired receptacles in 48' and 50'. Eliminates multiple splicing, speeding up installation on long runs.

Customization available. All products can be modified to accommodate virtually any application.

Compact, low profile appearance. Requires minimal space.

Full range of fittings. Provides a complete wiring solution.

Factory wired Plugmold® sections available in 3', 5', and 6' lengths with 15A receptacles installed in cover. Ideal for short runs requiring additional outlets in electrically busy areas.

Choice of receptacle spacing. Center spacing between receptacles of 6", 9", 12", and 18".

Snapicoil harnesses offer a choice of receptacle spacing. Center spacing between receptacles of 12", 18" and 30".

This product meets the material restrictions of RoHS.

Specifications

General Info

Product Line	Wiremold	UPC Number	786776084894
Country Of Origin	United States	Number of Receptacles	5

cULus Listed Base & Blank Cover: File E4376
Guide RJBT. Multioutlet Assemblies: File E15191
Guide PVGT. Fittings: File E41751
Guide RJPR. Base & Blank Cover & Plugmold Series w/Snapcoil Harness:
Meets Article 386 of NEC.
Meets Section 12-3032 of CEC. Plugmold Wired Sections: Meets Article 380 of NEC. Meets Section 12-3032 of CEC.

Application Sector Commercial Standard

Type Plugmold

Dimensions

Product Weight US 3.03 lb

Listing Agencies / 3rd Party Agencies

cULus ListingNumber E15191 cULus Listed Yes

Trade Programs

USMCA Yes

Additional Information

RoHS Compliant Yes Product Environmental Profile Yes

Technical Information

Amperage 15 A Enclosure Type Stainless Steel

Voltage 125.0 V Environmental Conditions Dry interior locations