



Pass and Seymour  
Discontinued - Fed Spec Grade USB Chargers w/ Tamper-Resistant 20A Receptacle, Ivory  
Part No. TR5361USBI



Designed for commercial markets with strength and durability in mind, this combination USB charger receptacle features 2.1A overall USB charging capability and is compatible with USB 2.0 & 3.0 devices.

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles page](#).

Features & Benefits

|   |   |
|---|---|
| 2.1 A USB type A receptacle charges faster than other USB receptacles eliminates the need for bulky AC adapters.                              | Compact Design Tamper-Resistant receptacle and two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices.                                       |
| Back and side wire terminals accommodates #14 AWG - #10 AWG stranded and solid wire.  | Tamper-Resistant, patented shutter system prevents improper insertion of foreign objects. Meets 2011 National Electrical Code: Tamper-Resistant requirements. |
| Stainless steel auto-ground clip assures positive ground.   | Zink-plated ground terminal screw   |
| For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> . Wire Size: #14 - #10 AWG Copper Conductor Only |   |

Specifications

General Info

|                    |                |                         |  |
|--------------------|----------------|-------------------------|--|
| Product Line       | Pass & Seymour | Replaced by Part Number | TR5362USBI                                   |
| Color              | Ivory          | Country Of Origin       | China  |
| Application Sector | Commercial     | Standard                | CSA Listed, ETL Lsted, FSUL, UL Listed, RoHS |

Additional Information

Product Environmental Profile Yes

Technical Information

|                          |                          |                     |                   |
|--------------------------|--------------------------|---------------------|-------------------|
| Dielectric Strength      | Withstands 2000V minimum | Is Tamper-Resistant | Yes               |
| Phase                    | Single                   | Connection          | Side & Back Wired |
| Number of Wires          | 3                        | Temperature Rating  | -40° - 60° C      |
| Amperage                 | 20 A                     | Number of Poles     | Double Pole       |
| Wire Size                | 14 - 10 AWG              | Voltage             | 125.0 V           |
| Environmental Conditions | UL94 V2                  |                     |                   |