



Tamper-Resistant Hard Use Spec Grade Receptacle, Back and Side Wire, 20A, 125V

## Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects.	Exclusive patented feature, circuit label on face allows permanent circuit identification.
Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.	Backed-out tri-drive brass terminal screws for faster installation.
Internal screw-pressure-plate back and side wire capability.	Two back wire holes for additional wiring flexibility.
.032 inch thick brass triple-wipe power contacts.	Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.
For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> .	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007243710
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Tamper-Resistant	Application Sector	Commercial
Standard	UL 498	Warranty Type	1-Year Limited Warranty
Type	Outlet		

### Dimensions

Product Width US	1.322 in	Product Depth US	1.13 in
Product Height US	2.635 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Phase	Three
---------------------	-----	-------	-------

Number of Wires	3	Amperage	20 A
-----------------	---	----------	------

Number of Poles	Double Pole	Wire Size	14 - 10 AWG
-----------------	-------------	-----------	-------------

Indoor/Outdoor	Indoor		
----------------	--------	--	--