




Pass and Seymour
Hard-Use Spec Grade Plug Load Controllable Receptacle, 20A, 125V, Ivory
Part No. TR5362CDI



Permanent controlled receptacle marking allows for long-lasting, easy identification of controlled receptacle for end-users. NEMA-approved and compliant with NEC, CA Title 24, and ASHRAE Energy Efficiency Standard 90.1.

Features & Benefits

| | |
|---|--|
| Can be wired to any number of system-based or stand-alone plug load control solutions. | Corrosion-resistant, plated and tabbed steel strap locked in to face and back body to resist pulling away from face/body assembly. |
| .032 inch thick, brass, triple-wipe power contacts for lasting retention. | Permanent controlled receptacle markings using abrasion resistant ink. |
| Two drive screws anchor strap to back body and face where abrupt removal torque is strongest. | Tri-drive brass-plated terminal screws. Two back-wire holes for more wiring flexibility. |
| Dual mechanical shutter system to help prevent insertion of foreign objects (for Tamper-Resistant models). | Strap tabs wrap around face to prevent strap from separating from face and back body. |
| CH Version Only: Split circuit tab broken at the factory, allowing half of the receptacle to be controlled. | For covering patents, see www.legrand.us/patents . |
| For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here . | |

Specifications

General Info

| | | | |
|--------------|----------------|-------------------|--------|
| Product Line | Pass & Seymour | Color | Ivory |
| UPC Number | 785007051131 | Country Of Origin | Mexico |
| Standard | FEDSPEC | | |

Dimensions

| | | | |
|------------------|----------|------------------|---------|
| Product Width US | 1.322 in | Product Depth US | 0.78 in |
|------------------|----------|------------------|---------|

Product Height US 2.635 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber 140596 cULus Listed Yes

Technical Information

Amperage 20 A
