




Pass and Seymour  
KL Series Locking Switch Plate, Two Gang, 302/304 Stainless Steel  
Part No. SS727

Double gang wallplate for Key Locking Series lock switch.  
Smooth 302/304 Stainless steel.



### Features & Benefits

- Type 302/304 Stainless Steel, non-magnetic: .032"  
nominal thickness.
- Brushed finish.
- This alloy contains 18% chromium and 8% nickel  
for superior resistance to corrosion.
- Recommended for use in food processing plants, dairies, chemical plants,  
and other industrial, institutional, and commercial applications where  
corrosive atmospheres exist.
- Standard, Jumbo, and Tandem plates available, as  
well as special Panel plates up to 5-gangs high and 10-gangs wide.
- Packaged in protective film, with finish-matching screws.
- Variety of special plated finishes.
- Paintable to match plastic plates.
- Can be silk-screened or engraved, and custom  
punched with over 300 opening styles.

### Specifications

#### General Info

Product Line	Pass & Seymour	Country Of Origin	United States
Application Sector	Residential/Commercial	Standard	CSA

#### Dimensions

Product Width US	4.56 in	Product Depth US	0.2 in
Product Height US	4.5 in		

#### Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

Technical Information

---

Cutout	For KL Series Locking Switch ONLY	Thickness	0.032 in
--------	-----------------------------------	-----------	----------

---

Number of Gangs	2
-----------------	---

---