

Straight male, liquid tight grips for non-metallic type A flexible conduit. 1/2-inch NPT, 10-inch Mesh Length.



Features & Benefits

Liquid-Tight grips are woven of stainless steel mesh with zinc plated steel or malleable iron bodies and nuts for corrosion resistance.

Each fitting is supplied with an insulated throat to provide conductor insulation and protect against damage by flexing, heat expansion and contraction.

They are used to connect liquid-tight flexible conduit to electrical enclosures to prevent conduit pullout.

Liquid-Tight grips are recommended in the wiring of motors and any electrical enclosure where liquid-tight conduit is subject to motion or strain.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007185454
Country Of Origin	Mexico	Construction	Various Types of Pulling, Support and Strain Relief Grips
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
------------	-----	--------------	-----

Technical Information

Capacity	Various Cable Diameter Ranges	Cable Size	NPT Size: 1/2; Mesh Length: 10
----------	-------------------------------	------------	--------------------------------

Mounting

Consult the Factory for Mounting
Recommendations

Load

Strain Relief Grips are designed to prevent tension from being transferred to junctions and terminals on electrical cord, cable and conduit, therefore providing a more secure electrical structure.
