



radiant Collection
radiant® 15A Tamper-Resistant USB Outlet, White
Part No. TM826USBWCCV6



Get a full battery for your phones, tablets and more with the convenience of built-in charging. This tamper-resistant USB outlet includes two USB Type-A connections and replaces traditional outlets in as little as ten minutes, providing easy-to-access charging without needing bulky adapters or sacrificing your plugs. Also features the sleek, clean lines of radiant® for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Provides convenient built-in charging, without sacrificing plugs or requiring a bulky adapter.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

All Legrand USB Outlets are manufactured through high-quality design, sourcing and production, and backed by a Lifetime Warranty.

Replaces a traditional outlet easily, in as little as 10 minutes, with features like scalloped cover design and posted side-wire terminal screws for faster installation.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

| | | | |
|--------------------|------------------------|-----------------------|---|
| Product Line | Pass & Seymour | Color | White |
| Country Of Origin | Vietnam | Number of Receptacles | 2 |
| Features | USB-A Charging | Outlet Type | Indoor, Residential, Tamper-Resistant, USB-Charging |
| Application Sector | Residential/Commercial | Warranty Type | 1-Year Limited Warranty |
| Type | Outlet | | |

Dimensions

| | | | |
|------------------|---------|------------------|---------|
| Product Width US | 1.69 in | Product Depth US | 1.35 in |
|------------------|---------|------------------|---------|

| | |
|-------------------|---------|
| Product Height US | 4.18 in |
|-------------------|---------|

Technical Information

| | | | |
|---------------------|-----|--------------|-------|
| Is Tamper-Resistant | Yes | USB Amperage | 3.1 A |
|---------------------|-----|--------------|-------|

| | | | |
|----------------|---|-----------------|---|
| Number of USBs | 2 | Number of Gangs | 1 |
|----------------|---|-----------------|---|

| | | | |
|------------------|------|----------|------|
| USB Power Output | 15 W | Amperage | 15 A |
|------------------|------|----------|------|

| | | | |
|-----------------|-------------|----------------|--------|
| Number of Poles | Double Pole | Indoor/Outdoor | Indoor |
|-----------------|-------------|----------------|--------|

| | |
|---------|---------|
| Voltage | 125.0 V |
|---------|---------|
