



radiant Collection  
radiant® 15A 3-Way Switch with Locator Light, Light Almond  
Part No. TM873LASL



Perfect for use in larger rooms like master suites and foyers, this 3-way switch allows for control of a single light or fixture from two separate switches. It also includes a small, built-in light for easily locating in the dark. Part of the radiant® Collection, it features clean lines and smooth paddle action for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

For use with incandescent lights/bulbs only.	Replaces any standard switch with ease, in as little as 10 minutes.
Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.	Uses a paddle switch for smoother control with a low-profile aesthetic.
Features durable, high-impact resistant thermoplastic construction.	Designed to install easily with a narrower back body and captivated mounting screws.
More color options available to fit any style, including finishes to match current hardware and lighting trends.	Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Light Almond
Country Of Origin	China	Features	Nightlight
Switch Type	Paddle	Number of Switches	1
Application Sector	Residential/Commercial	Standard	UL 20
Warranty Type	1-Year Limited Warranty	Type	Switch

### Dimensions

Product Width US	1.43 in	Product Depth US	1.27 in
------------------	---------	------------------	---------

Product Height US	4.19 in
-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Number of Gangs	1	Amperage	15 A
-----------------	---	----------	------

Number of Poles	3-Way, Single Pole	Indoor/Outdoor	Indoor
-----------------	--------------------	----------------	--------

Mounting Type	Box	Voltage	120/277 V
---------------	-----	---------	-----------