



Tamper-Resistant Hospital Grade Receptacles, Smooth Face, Back and Side-Wire, 15A, 125A



Features & Benefits

Thermoplastic dual mechanism shutter system to help prevent insertion of foreign objects.

Smooth face.

Exclusive patented feature, circuit label on face allows permanent circuit identification.

Extra heavy-duty brass, one-piece mounting strap with integral ground.

One-piece, nickel-plated brass, triple-wipe power contacts for lasting retention.

Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.

Impact-resistant nylon face and back body.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Two drive screws anchor strap to back body and face.

Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line

Pass & Seymour

Color

Gray

| | | | |
|--|-------------|--------------------|-------------|
| Country Of Origin | Mexico | Application Sector | Commercial |
| Standard | UL 498 | | |
| Dimensions | | | |
| Product Width US | 1.625 in | Product Depth US | 0.9 in |
| Product Height US | 2.75 in | | |
| Listing Agencies / 3rd Party Agencies | | | |
| cULus ListingNumber | 140596 | cULus Listed | Yes |
| Technical Information | | | |
| Is Tamper-Resistant | Yes | Phase | 3 |
| Number of Wires | 3 | Amperage | 15 A |
| Number of Poles | Double Pole | Wire Size | 14 - 10 AWG |
| Voltage | 125.0 V | | |