



Tamper-Resistant Heavy-Duty Decorator Spec Grade Single Receptacle, Back and Side Wire, 20A, 125V



Features & Benefits

| | |
|--|---|
| Dual mechanical shutter system to help prevent insertion of foreign objects. | Two drive screws anchor strap to back body and face where abrupt removal torque is greatest. |
| Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring. | Backed-out tri-drive brass terminal screws for faster installation. |
| Internal screw-pressure-plate back and side wire capability. | Two back wire holes for additional wiring flexibility. |
| .032 inch thick brass triple-wipe power contacts. | Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest. |
| For covering patents, see www.legrand.us/patents . | Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact |

Specifications

General Info

| | | | |
|-------------------|-------------------------|-----------------------|--------------|
| Product Line | Pass & Seymour | UPC Number | 785007004854 |
| Country Of Origin | Mexico | Number of Receptacles | 2 |
| Outlet Type | Tamper-Resistant | Application Sector | Commercial |
| Standard | UL498, CSA C22.2 No. 42 | Type | Outlet |

Dimensions

| | | | |
|------------------|----------|------------------|----------|
| Product Width US | 1.322 in | Product Depth US | 1.188 in |
|------------------|----------|------------------|----------|

Product Height US 2.635 in

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

| | | | |
|---------------------|--------------------------|--------------------------|-----------------------|
| Dielectric Strength | Withstands 2000V minimum | Is Tamper-Resistant | Yes |
| Connection | Back and side wire | Number of Wires | 3 |
| Temperature Rating | -40° - 60° C | Amperage | 20 A |
| Number of Poles | Double Pole | Wire Size | 14 - 10 AWG |
| Indoor/Outdoor | Indoor | Environmental Conditions | Flammability: UL94 V2 |
