



Tamper-Resistant Heavy-Duty Decorator Spec Grade Single Receptacle, Back and Side Wire, 20A, 125V

### Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects.	Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.	Backed-out tri-drive brass terminal screws for faster installation.
Internal screw-pressure-plate back and side wire capability.	Two back wire holes for additional wiring flexibility.
.032 inch thick brass triple-wipe power contacts.	Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.
For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> .	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

### Specifications

#### General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Number of Receptacles	2	Outlet Type	Commercial, Indoor, Tamper-Resistant
Application Sector	Commercial	Standard	UL498, CSA C22.2 No. 42
Type	Outlet		

#### Dimensions

Product Width US	1.322 in	Product Depth US	1.188 in
------------------	----------	------------------	----------

Product Height US	2.635 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Is Tamper-Resistant	Yes
---------------------	--------------------------	---------------------	-----

Connection	Back and side wire	Number of Wires	3
------------	--------------------	-----------------	---

Temperature Rating	-40° - 60° C	Amperage	20 A
--------------------	--------------	----------	------

Number of Poles	Double Pole	Wire Size	14 - 10 AWG
-----------------	-------------	-----------	-------------

Indoor/Outdoor	Indoor	Voltage	125.0 V
----------------	--------	---------	---------

Environmental Conditions	Flammability: UL94 V2
--------------------------	-----------------------