



Tamper-Resistant Isolated Ground Decorator Hospital Grade Duplex Receptacle, Back & Side Wire, 20amp 125volt, White. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

IG symbol and Isolated Ground markings for easy identification and circuit delineation.	Triple-wipe brass contacts ensure lasting, positive contact with plug blades.
High-impact resistant nylon face resists impacts and scrapes.	Corrosion-resistant plated steel strap.
Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.	Plastic barrier isolates grounding terminal from mounting strap and metal boxes.
Side and internal screw-pressure-plate back wire capability with #14 - #10 AWG copper or copper-clad, solid or stranded wire.	Auto-ground clip assures positive ground.
For covering patents, see www.legrand.us/patents .	For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here .

Specifications

General Info

Product Line	Pass & Seymour	Color	Orange
UPC Number	785007012538	Country Of Origin	Mexico
Application Sector	Commercial	Standard	cULus UL498

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Connection	Back and side wire
Number of Wires	3	Temperature Rating	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact
Number of Poles	Double Pole	Wire Size	#14 - #10
Voltage	125 V	Environmental Conditions	Flammability: UL94 V2