



Legrand

20A Extra Heavy-Duty Decorator Power Indicating Hospital-Grade Receptacle, Gray

Part No. TR26362HGPIGRY



Built for the harshest medical environments, P&S power indicating receptacles feature two industry-exclusive green LEDs that offer clear visual assurance of power indication at the receptacle even with critical equipment plugged into the device. The LEDs operate independently from one another to accommodate split-circuit wiring installations. Tamper-resistant protection comes standard with each receptacle to further enhance safety.

Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects.

Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.

Internal screw-pressure-plate back and side wire capability.

Corrosion-resistant plated steel strap is locked in to face and back body to resist pulling away from the face/body assembly.

Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Auto-ground clip assures positive ground.

Backed-out tri-drive brass terminal screws for faster installation.

Two back wire holes for additional wiring flexibility.

.032 inch thick brass triple-wipe power contacts.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Color Gray

UPC Number 785007041538

Country Of Origin Mexico

Product Line Pass & Seymour

Application Sector Hospital Grade

Standard UL Listed, CSA Listed, cULus, FSUL

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Number of Poles Double Pole

Voltage 125 V

Connection	Side & Back Wired
-------------------	-------------------

Dielectric Strength	Withstands 2000V minimum
----------------------------	--------------------------

Phase	Single
--------------	--------

Temperature Rating	Maximum continuous +60°C, minimum -40° without impact
---------------------------	---

Wire Size	#14 -#10 AWG Copper Conductor Only
------------------	------------------------------------

Number of Wires	3
------------------------	---

Environmental Conditions	UL94 V2
---------------------------------	---------
