



Pass and Seymour

20A 125V Heavy Duty Hospital-Grade Tamper-Resistant Decorator Duplex Receptacle, Back and Side Wire, White

Part No. TR26362HGW

Tamper-Resistant Heavy-Duty Decorator Hospital Grade Receptacles, Back and Side Wire, 20A, 125V



## Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects.

Auto-ground clip assures positive ground.

Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.

Backed-out tri-drive brass terminal screws for faster installation.

Internal screw-pressure-plate back and side wire capability.

Two back wire holes for additional wiring flexibility.

.032 inch thick brass triple-wipe power contacts.

Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007277456
Country Of Origin	Mexico	Number of Receptacles	2
Outlet Type	Tamper-Resistant	Application Sector	Commercial, Hospital Grade
Standard	UL498, cUL CSA, FEDSPEC	Type	Outlet

### Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

---

## Technical Information

---

Dielectric Strength	Withstands 2000V minimum	Is Tamper-Resistant	Yes
Temperature Rating	-40° - 60° C	Amperage	20 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor		

---