



Tamper-Resistant Hard Use Spec Grade Receptacle, Back and Side Wire, 20A, 125V

Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects.	Exclusive patented feature, circuit label on face allows permanent circuit identification.
Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.	Backed-out tri-drive brass terminal screws for faster installation.
Internal screw-pressure-plate back and side wire capability.	Two back wire holes for additional wiring flexibility.
.032 inch thick brass triple-wipe power contacts.	Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.
For covering patents, see www.legrand.us/patents .	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Number of Receptacles	2	Outlet Type	Commercial, Indoor, Tamper-Resistant
Application Sector	Commercial	Standard	UL 498
Warranty Type	1-Year Limited Warranty	Type	Outlet

Dimensions

Product Width US	1.322 in	Product Depth US	1.13 in
Product Height US	2.635 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Phase	3
Number of Wires	3	Amperage	20 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	Voltage	125.0 V