



Pass and Seymour
20A 125V Extra Heavy Duty Tamper-Resistant Surge Protective Duplex Receptacle, Ivory
Part No. TR5362ISP



Tamper-Resistant Extra Heavy-Duty Surge Protective Duplex Receptacle offers increased transient protection, reliability and protection notification (with Audible Alarm and LED Indicator), Back and Side Wire, 20A, 125V. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Dual mechanical shutter system to help prevent insertions of foreign objects.

.032 inch thick brass triple-wipe power contacts for lasting retention.

Auto-ground clip assures positive ground.

AC receptacles available in 15 and 20 Amp, 125V

Corrosion-resistant plated steel strap is locked in to the face and back body to resist pulling away from the face/body assembly.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007020281
Country Of Origin	China	Application Sector	Commercial, Residential

Dimensions

Product Width US	1.7 in	Product Depth US	1.4 in
Product Height US	2.75 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Phase	Single	Connection	Side & Back Wire
-------	--------	------------	------------------

Class	IG	Amperage	20 A
Type of Indicators	Audible Alarm, LED	Environmental Conditions	UL94 V2