



Pass and Seymour  
**Tamper-Resistant Isolated Ground Hospital Grade Receptacle, Back and Side Wire, 20A, 125V, Red**  
Part No. TRIG8300RED



Tamper-Resistant Isolated Ground Hospital Grade Duplex Receptacle, Back & Side Wire, 20amp 125volt, Orange. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

## Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects.

Auto-ground clip assures positive ground.

Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.

Backed-out tri-drive brass terminal screws for faster installation.

Internal screw-pressure-plate back and side wire capability.

Two back wire holes for additional wiring flexibility.

Corrosion-resistant plated steel strap is locked in to face and back body to resist pulling away from the face/body assembly.

.032 inch thick brass triple-wipe power contacts.

Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

|                    |                |                   |             |
|--------------------|----------------|-------------------|-------------|
| Product Line       | Pass & Seymour | Color             | Red         |
| UPC Number         | 785007012491   | Country Of Origin | Mexico      |
| Application Sector | Commercial     | Standard          | cULus UL498 |

### Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

### Technical Information

---

|                     |                          |                          |  |
|---------------------|--------------------------|--------------------------|--|
| Dielectric Strength | Withstands 2000V minimum | Connection               | Back and side wire   |
| Number of Wires     | 3                        | Temperature Rating       | Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.<br>Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact |
| Number of Poles     | Double Pole              | Wire Size                | #14 - #10  |
| Voltage             | 125 V                    | Environmental Conditions | Flammability: UL94 V2  |

---