



**Pass and Seymour**  
**20A 125V Extra Heavy Duty Tamper-Resistant Surge Protective Duplex Receptacle, Ivory**  
Part No. TR5362ISP



Tamper-Resistant Extra Heavy-Duty Surge Protective Duplex Receptacle offers increased transient protection, reliability and protection notification (with Audible Alarm and LED Indicator), Back and Side Wire, 20A, 125V. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

## Features & Benefits

Dual mechanical shutter system to help prevent insertions of foreign objects.

.032 inch thick brass triple-wipe power contacts for lasting retention.

Auto-ground clip assures positive ground.

AC receptacles available in 15 and 20 Amp, 125V

Corrosion-resistant plated steel strap is locked in to the face and back body to resist pulling away from the face/body assembly.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

|              |                |                   |       |
|--------------|----------------|-------------------|-------|
| Product Line | Pass & Seymour | Country Of Origin | China |
|--------------|----------------|-------------------|-------|

|                    |                        |
|--------------------|------------------------|
| Application Sector | Residential/Commercial |
|--------------------|------------------------|

### Dimensions

|                  |        |                  |        |
|------------------|--------|------------------|--------|
| Product Width US | 1.7 in | Product Depth US | 1.4 in |
|------------------|--------|------------------|--------|

|                   |         |
|-------------------|---------|
| Product Height US | 2.75 in |
|-------------------|---------|

### Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

### Technical Information

|       |        |                  |       |
|-------|--------|------------------|-------|
| Phase | Single | Frequency Rating | 60 Hz |
|-------|--------|------------------|-------|

---

|            |                  |                          |                    |
|------------|------------------|--------------------------|--------------------|
| Connection | Side & Back Wire | Class                    | IG                 |
| Amperage   | 20 A             | Type of Indicators       | LED, Audible Alarm |
| Voltage    | 125.0 V          | Environmental Conditions | UL94 V2            |

---