



Tamper-Resistant Hard Use Spec Grade Receptacle, Back and Side Wire, 20A, 125V

Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects.

Exclusive patented feature, circuit label on face allows permanent circuit identification.

Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.

Backed-out tri-drive brass terminal screws for faster installation.

Internal screw-pressure-plate back and side wire capability.

Two back wire holes for additional wiring flexibility.

.032 inch thick brass triple-wipe power contacts.

Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

| | | | |
|-------------------|-------------------------|-----------------------|-------------------------|
| Product Line | Pass & Seymour | Color | Red |
| Finish | Matte | UPC Number | 785007243734 |
| Country Of Origin | Mexico | Number of Receptacles | 2 |
| Outlet Type | Tamper-Resistant | Application Sector | Commercial |
| Standard | UL498, CSA C22.2 No. 42 | Warranty Type | 1-Year Limited Warranty |
| Type | Outlet | | |

Dimensions

| | | | |
|---------------------------------------|--------------------------|---------------------|-------------|
| Product Width US | 1.322 in | Product Depth US | 1.13 in |
| Product Height US | 2.635 in | | |
| Listing Agencies / 3rd Party Agencies | | | |
| cULus ListingNumber | 140596 | cULus Listed | Yes |
| Technical Information | | | |
| Dielectric Strength | Withstands 2000V minimum | Is Tamper-Resistant | Yes |
| Temperature Rating | -40° - 60° C | Amperage | 20 A |
| Number of Poles | Double Pole | Wire Size | 14 - 10 AWG |
| Indoor/Outdoor | Indoor | | |