



## Pass and Seymour Fed Spec Grade USB Charger w/ Tamper-Resistant 20A Duplex Receptacles, Nickel Part No. TR5362USBNI



Designed for commercial markets with strength and durability in mind, this combination USB charger duplex receptacle features 3.1A overall USB charging capability and is compatible with USB 2.0 & 3.0 devices. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

### Features & Benefits

Overall 3.1A USB charging capability: Combination AC duplex receptacles include two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices.

AC receptacles available in 15 and 20A, 125V.

AC receptacles are tamper-resistant as standard: patented shutter system prevents improper insertion of foreign objects.

Multiple color options available.

Back and side wire terminals accommodate #14 AWG - #10 AWG stranded and solid copper wire.

Stainless steel auto-ground clips assure positive ground.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### Specifications

#### General Info

Color	Nickel	UPC Number	785007031652
Country Of Origin	China	Product Line	Pass & Seymour
Application Sector	Commercial	Standard	CSA Listed, cULus, FSUL, UL Listed, RoHS

#### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

#### Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

#### Technical Information

Number of Poles	Double Pole	Voltage	125 V
Connection	Side & Back Wired	Dielectric Strength	Withstands 2000V minimum
Phase	Single	Temperature Rating	Maximum continuous +60°C, minimum -40° without impact
Wire Size	#14 -#10 AWG Copper Conductor Only	Number of Wires	3

