



Replace your standard switch with the new Toggle Slide Dimmer by Legrand. The new Toggle Slide Dimmer offering has been optimized for today's complicated dimmable bulb market. Different bulbs require different dimming solutions and Legrand has you covered for all your lighting needs. The ergonomic slider was designed with the end user in mind, making it easier to adjust in the dark or on the run.

Compatible with CFL/LED and Incandescent/Halogen dimmable bulbs (with the exception of 0-10V LED drivers), these dimmers feature constant memory that returns lights to the previous level after a power failure for automatic control and convenience.

## Features & Benefits

No neutral wire required	Calibration button allows users to adjust minimum and maximum trim levels for a wide range of CFL and LED bulbs
New aesthetically pleasing ergonomic design allows for easier operation	Constant memory returns lights to previous levels after a power failure
Convenient operation – combines ON/OFF toggle switch with separate slider for dimming control	Screw-pressure-plate backwire terminals save time, space and money
Preset, Single Pole and 3-Way operation.	Lifetime warranty

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Ivory, Light Almond, White
Finish	Matte	Country Of Origin	China
Switch Type	Rocker, Slider	Number of Switches	1
Application Sector	Commercial, Residential	Warranty Type	Limited Lifetime Warranty
Type	Dimmer		

### Dimensions

Product Width US	1.73 in	Product Depth US	1.4 in
Product Height US	4.19 in		

### Technical Information

Amperage	2.1 A	Bulb Compatibility	CFL, Halogen, Incandescent, LED
Number of Poles	3-Way, Single Pole	Wattage	300 W
Voltage	120.0 V		