



Wattstopper
Ultrasonic Ceiling Occupancy Sensor, 100-347VAC, 2000 sq ft
Part No. UT-355-3



Wattstopper's low-profile UT-355 Ultrasonic Line Voltage Ceiling Sensor automatically turns lighting on and off based on occupancy. The sensor mounts on the ceiling with a flat, unobtrusive appearance and provides 360° coverage.

Features & Benefits

Architecturally appealing low-profile appearance

Utilizes advanced, omni-directional, ultrasonic technology

Ultrasonic diffusers provide more comprehensive coverage

Operates at 120, 230 (single phase), 277 or 347 VAC, 50/60 Hz

Terminal wiring for quick and easy installation

Walk-through mode increases savings potential

Specifications

General Info

Product Line	Wattstopper	Color	White
Finish	Glossy	UPC Number	754182915224
Country Of Origin	China	Product Series	UT-355
Features	Adjustable Time Delay, Indicator Lights, Light Level Sensor, Sensitivity Adjustment	Installation Location	Ceiling
Included	Mounting Screws	Application Sector	Commercial
Standard	UL, cUL, PEP	Warranty Type	5-Year
Type	Sensor		

Dimensions

Product Width US	4.5 in	Product Weight US	0.337 lb
------------------	--------	-------------------	----------

Product Volume US	69.6 cu in	Product Depth US	1.9 in
Product Height US	4.5 in		

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

Technical Information

Operating Temperature Min	32 °F	Timer Type	DIP Switch
Load Rating	1200 W @ 230 VAC, 1200 W @ 277 VAC, 1500 W @ 347 VAC, 800 W @ 120 VAC	Ultrasonic Frequency	40 kHz
Has Battery	No	Sensor Coverage Pattern	360 deg
Sensor Type	Occupancy	Operating Temperature Max	131 °F
Sensor Mounting Height	8-10 ft	Number of Buttons	0
Number of Rockers	0	Sensor Technology	Ultrasonic
Timer Duration	30 Seconds, 5-30 Minutes	Indicator	Ultrasonic Detection LED
Input Voltage	120/230/277/347 VAC	Line Frequency	60 Hz
Indoor/Outdoor	Indoor	Sensor Coverage	2000 sq ft
Mounting Type	2-1/4 in Deep J-Box, Surface	On Function	Auto On
Operating Temperature	0°-55°C, 32°-131°F	Operating Humidity	5-95% RH (Non-Condensing)
Sensing Range	10 x 60 ft, 40 x 40 ft	Wire Connection Type	Screw Terminals
Engraving Type	Blank	Storage Temperature	23° - 176° F, -5° - 80° C