



Tamper-Resistant Spec Grade Receptacles, Back and Side-Wire, 15A, 125A

Features & Benefits

- Thermoplastic dual mechanism shutter system to help prevent insertion of foreign objects. Exclusive patented feature, circuit label on face allows permanent circuit identification.
- Extra heavy-duty brass, one-piece mounting strap with integral ground. One-piece, brass, triple-wipe power contacts for lasting retention.
- Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body. Impact-resistant nylon face and back body.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring. Two drive screws anchor strap to back body and face.
- Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation. External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.
- Auto-ground clip assures positive ground. For covering patents, see www.legrand.us/patents.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#). Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL 498

Dimensions

Product Width US	1.625 in	Product Depth US	0.9 in
------------------	----------	------------------	--------

Product Height US	2.75 in
-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Phase	3
---------------------	-----	-------	---

Number of Wires	3	Amperage	15 A
-----------------	---	----------	------

Number of Poles	Double Pole	Wire Size	14 - 10 AWG
-----------------	-------------	-----------	-------------

Voltage	125.0 V
---------	---------
